

Basic Ejector

SEG 15 HS

Part no.:10.02.01.00248

<https://www.schmalz.com/10.02.01.00248>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SEG > SEG 15 HS

Basic ejector with robust housing for universal use




Nozzle diameter: 1.5 mm

Shape: For high vacuum

Suction rate (max.): 69 l/min

Air consumption suction: 102 l/min

Design Data



Attribute	Value
B	22 mm
D	20 mm
G1	G1/4"-F
G2	G1/4"-F
G3	G1/4"-F
H	38 mm
L	75 mm
SW1	17 mm

Technical Data

Attribute	Value
Nozzle diameter	1.50 mm
Degree of evacuation	85 %
Suction rate (max.)	69 l/min
Suction rate (max.)	4.10 m³/h
Air consumption suction	102 l/min
Air consumption suction	6.10 m³/h
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure range (operating pressure)	43.5 ... 87.0
Pressure optimal	5 bar

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Basic Ejector

SEG 15 HS

Part no.:10.02.01.00248

<https://www.schmalz.com/10.02.01.00248>

Pressure optimal	72.50 psi
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Operating temperature	-10 ... 80 °C
Weight	102 g
Product family	SEG

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



VFT G1/4-IG 80

Part no.:10.07.01.00119

Connection: G1/4"-F

Shape: Short filter insert

Nominal flow rate: 110 l/min

Nominal flow rate: 6.6 m³/h

Filter pore size: 80 µm