

Vacuum gauge (electronic)

VAM-D 30x30 VP10 G1/8-AG

Part no.:10.07.02.00055

<https://www.schmalz.com/10.07.02.00055>

Home > Vacuum Technology for Automation > Vacuum Components > Switches and System Monitoring > Measuring and Control Devices > Manometers VAM-D > VAM-D 30x30 VP10 G1/8-AG

Vacuum gauge (manometer) for measurement and monitoring of the vacuum




Length L: 30 mm

Width B: 30 mm

Measuring range: -1,0 ... 10,0 bar

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
B	30 mm
G1	G1/8"-M
G2	M5-F
G4	M3-F
H	21.80 mm
H1	37 mm
L	30 mm
LG1	5.60 mm
LG2	9.30 mm
LG4	4 mm
SW1	12 mm
X1	20 mm
Y1	20 mm

Technical Data

Attribute	Value
Operating temperature	0 ... 50 °C
Weight	40 g
Overpressure resistance	3 bar
Measured medium	Non-aggressive gases; dry, oil-free air

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Vacuum gauge (electronic)

VAM-D 30x30 VP10 G1/8-AG

Part no.:10.07.02.00055

<https://www.schmalz.com/10.07.02.00055>

Measuring range	-1,0 ... 10,0 bar
Measured-value display	3-digit 7-segment LED
Protection type IP	IP 40/65 (with hose)
Repeatability	± 1% of full-scale value
Product family	VAM-D

Accessories



BEF-WIN 13x50x31 1.6 VS

Part no.:10.06.02.00425

Length L: 31 mm

Width B: 13 mm

Height H: 50 mm

Wall thickness s: 1.6 mm

Construction use: Vacuum switch



EINB-RAx8.5x30 VS

Part no.:10.06.02.00427

Width B: 8.5 mm

Height H: 30 mm

Construction use: Vacuum switch