

Hose sleeve

ST G1/8-AG 6 MS-V

Part no.:10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/8-AG 6 MS-V

Hose sleeve



Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm


Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4.4 mm

Design Data



Attribute	Value
dn	4.40 mm
D	5.40 mm
G1	G1/8"-M
L	5 mm
L1	34 mm
LG1	8 mm
SW1	14 mm

Technical Data

Attribute	Value
Material	Brass
Weight	13 g

Accessories

Contact Schmalz


Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Hose sleeve

ST G1/8-AG 6 MS-V

Part no...:10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>



VSL 6-4 PE BL

Part no...:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no...:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no...:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz


Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Hose sleeve

ST G1/8-AG 6 MS-V

Part no.: 10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>



VSL 8-6 PE BL

Part no.: 10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.: 10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C