

Flat suction cup (oval)

SGON 18x6 NBR-ESD-55 M5-IG

Part no.:10.01.05.00944

<https://www.schmalz.com/10.01.05.00944>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 18x6 NBR-ESD-55 M5-IG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-F

Design Data



Attribute	Value
Bmax(S)	7 mm
Bs	6 mm
dn	1.50 mm
G1	M5-F
H	22 mm
LG1	5.50 mm
Lmax(S)	18.50 mm
Ls	18 mm
SW1	8 mm
Z (Stroke)	0.80 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	4.50 N
Volume	0.21 cm ³
Curve radius (min) (convex)	4 mm
Hose diameter (rec.) d	2 mm
Number of folds	0
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Flat suction cup (oval)

SGON 18x6 NBR-ESD-55 M5-IG

Part no.:10.01.05.00944

<https://www.schmalz.com/10.01.05.00944>

Weight	3.80 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SGO 18x6 NBR-ESD-55 N021

Part no.:10.01.05.00932

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A



SA-NIP N021 M5-IG DN200

Part no.:10.01.05.00125

Thread G1: M5-F

Length L1: 15.5 mm

Fitting length: 10 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au