

## Feed ejector

SEC-400

Part no.:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-400


### Powerful ejector for very porous parts



Nozzle size: 40 mm

Suction rate (max.): 135 m³/h

### Design Data



| Attribute | Value   |
|-----------|---------|
| D         | 84 mm   |
| D1        | 75 mm   |
| D2        | 52 mm   |
| G2        | G3/8"-F |
| G3        | M4-F    |
| L         | 35 mm   |
| L1        | 95 mm   |
| LG3       | 14 mm   |
| X1        | 72 mm   |

### Technical Data

| Attribute                           | Value           |
|-------------------------------------|-----------------|
| Max. vacuum                         | -25 mbar        |
| Suction rate (max.)                 | 2250 l/min      |
| Suction rate (max.)                 | 135 m³/h        |
| Air consumption suction             | 500 l/min       |
| Air consumption suction             | 26.70 m³/h      |
| Pressure range (operating pressure) | 2.0 ... 6.0 bar |
| Operating temperature               | -20 ... 80 °C   |
| Weight                              | 0.53 kg         |
| Max. vacuum                         | -0.74 inHg      |

### Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | [schmalz@schmalz.com.au](mailto:schmalz@schmalz.com.au)

## Feed ejector

SEC-400

Part no.:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

|                                     |               |
|-------------------------------------|---------------|
| Suction rate (max.)                 | 79.46 cfm     |
| Air consumption suction             | 17.66 cfm     |
| Pressure range (operating pressure) | 29.0 ... 87.0 |
| Product family                      | SEC           |

Note: Air consumption: At optimal operating pressure (4,5 bar)

---