

Bellows suction cups (round)

SAXB 120 ED-85 M10-AG

Part no...:10.01.42.00062

<https://www.schmalz.com/10.01.42.00062>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows suction cups SAXB > SAXB 120 ED-85 M10-AG

High-speed bellows suction cup for adaptation to strongly curved and oiled surfaces



Size: 120

Suction cup material: Elastodur ED


Material hardness [Shore A]: 85 Shore A

Nipple material: Steel

Connection: M10-AG

Number of folds: 1.5

Design Data



Attribute	Value
Dmax(S)	131 mm
Ds	120.60 mm
D1	95 mm
G1	M10-M
H	67.80 mm
LG1	12 mm
SW1	22 mm
Z (Stroke)	32 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	275 N
Lateral force	479 N
Lateral force (oily surface)	380 N
Volume	251.70 cm ³
Curve radius (min) (convex)	67.50 mm
Hose diameter (rec.) d	4 mm
Size	120
Connection	M10-M

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cups (round)

SAXB 120 ED-85 M10-AG

Part no...:10.01.42.00062

<https://www.schmalz.com/10.01.42.00062>

Number of folds	1.50
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	130.30 g
Product family	SAXB