

## Non-return valve

RSV 18 G1/2-IG MS

Part no...:10.05.05.00003

<https://www.schmalz.com/10.05.05.00003>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices VacuMaster > Spare and Wear Parts VacuMaster Window 200/300 > RSV 18 G1/2-IG MS

### No-return valve for maintaining the system vacuum in the case of a power failure



Nominal size: 18 mm


Thread G1: G1/2"-F

Nominal flow rate: 26 m<sup>3</sup>/h

Operating temperature: -20 ... 100 °C

Material: Brass

### Design Data



| Attribute | Value    |
|-----------|----------|
| D         | 34.50 mm |
| G1        | G1/2"-F  |
| G2        | G1/2"-F  |
| L         | 58.50 mm |
| SW1       | 27 mm    |

### Technical Data

| Attribute         | Value                |
|-------------------|----------------------|
| Nominal size      | 18 mm                |
| Nominal flow rate | 26 m <sup>3</sup> /h |
| Nominal flow rate | 433.10 l/min         |
| Weight            | 0.19 kg              |
| Product family    | RSV                  |

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)