

Dust filter

STF 60 P 6.0 SSD

Part no.:10.07.01.00260

<https://www.schmalz.com/10.07.01.00260>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF 60 P 6.0 SSD

Dust filter



Connection: Ø60mm


Shape: Piclon housing

Nominal flow rate: 360 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	265 mm
B2	142 mm
d	8.50 mm
D	200 mm
D1	229 mm
D2	60 mm
D3	60 mm
H	253 mm
L	390 mm
L1	741 mm
L2	351 mm
X1	220 mm

Technical Data

Attribute	Value
Connection	Ø60mm
Nominal flow rate	360 m³/h
Nominal flow rate	6000 l/min
Max. vacuum	-500 mbar
Filter pore size	3 µm
Weight	2.40 kg

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Dust filter

STF 60 P 6.0 SSD

Part no.:10.07.01.00260

<https://www.schmalz.com/10.07.01.00260>

Product family

VF

Spare parts



FILT-EINS 3 149x361 PAP STF-Picl-6

Part no.:10.07.01.00054

Filter pore size: 3 µm

External diameter D: 149.2 mm

Length L: 360.5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: Picl-6

Type: 6



SSD 60-68 ST-VZ

Part no.:10.07.10.00017

Clamping range: 60.0 ... 68.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au