

Feed ejector

SEC-400

Part no.:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-400


Powerful ejector for very porous parts



Nozzle size: 40 mm

Suction rate (max.): 135 m³/h

Design Data



Attribute	Value
D	84 mm
D1	75 mm
D2	52 mm
G2	G3/8"-F
G3	M4-F
L	35 mm
L1	95 mm
LG3	14 mm
X1	72 mm

Technical Data

Attribute	Value
Max. vacuum	-25 mbar
Suction rate (max.)	2250 l/min
Suction rate (max.)	135 m³/h
Air consumption suction	500 l/min
Air consumption suction	26.70 m³/h
Pressure range (operating pressure)	2.0 ... 6.0 bar
Operating temperature	-20 ... 80 °C
Weight	0.53 kg
Max. vacuum	-0.74 inHg

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Feed ejector

SEC-400

Part no...:10.02.01.00080

<https://www.schmalz.com/10.02.01.00080>

Suction rate (max.)	79.46 cfm
Air consumption suction	17.66 cfm
Pressure range (operating pressure)	29.0 ... 87.0
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)
