

Bell suction cup (oval)

SAOG 95x40 NBR-45 G3/8-IG

Part no.:10.01.01.11615

<https://www.schmalz.com/10.01.01.11615>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAOG (Oval) > SAOG 95x40 NBR-45 G3/8-IG

Bell suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 95 x 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
Bmax(S)	46 mm
Bs	40 mm
dn	6 mm
G1	G3/8"-F
H	35.50 mm
LG1	9 mm
Lmax(S)	102 mm
Ls	95 mm
SW1	22 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	165 N
Lateral force	97 N
Lateral force (oily surface)	68 N
Volume	26.90 cm ³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	95 x 40

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Bell suction cup (oval)

SAOG 95x40 NBR-45 G3/8-IG

Part no.:10.01.01.11615

<https://www.schmalz.com/10.01.01.11615>

Suction cup material	Nitrile rubber NBR
Weight	47.30 g
Number of folds	0
Product family	SAOG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m