

Vacuum hose (meter)

VSL 60-50 PU-DS-AS KL-TR

Part no.:10.07.09.00020

<https://www.schmalz.com/10.07.09.00020>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 60-50 PU-DS-AS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 60 mm

Internal diameter d: 50 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.82 ... 2.48 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	50 mm
D	60 mm

Technical Data

Attribute	Value
Hose type	60-50
Pressure range (operating pressure)	-0.82 ... 2.48 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	35 mm
Length max.	20 m
Material hose	PU, wire spiral, antistatic
Product family	VSL

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum hose (meter)

VSL 60-50 PU-DS-AS KL-TR

Part no...:10.07.09.00020

<https://www.schmalz.com/10.07.09.00020>

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 60-68 ST-VZ

Part no...:10.07.10.00017

Clamping range: 60.0 ... 68.0 mm

Material: Steel

Surface: galvanised