

Vacuum filter (inline)

VFI CN6/4 50

Part no.:10.07.01.00241

<https://www.schmalz.com/10.07.01.00241>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Inline Filters VFI > VFI CN6/4 50


Vacuum filter with replaceable filter cartridge



Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm

Design Data



Attribute	Value
d	6 mm
D	16 mm
L	61 mm

Technical Data

Attribute	Value
Connection	Hose 6/4 with Cap nut
Filter pore size	50 µm
Nominal flow rate	32 l/min
Nominal flow rate	1.92 m³/h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Weight	6 g
Product family	VFI

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum filter (inline)

VFI CN6/4 50

Part no.:10.07.01.00241

<https://www.schmalz.com/10.07.01.00241>

Accessories



FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)

Spare parts



FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)