

Flat suction cup (round)

SUF 20 SI-CO-55 SC030

Part no...:10.01.01.14037

<https://www.schmalz.com/10.01.01.14037>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 20 SI-CO-55 SC030

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 20

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	7.30 mm
d	5.30 mm
Dk	12.50 mm
Dmax(S)	22.80 mm
Ds	20 mm
H	9.50 mm
H2	4.30 mm
H3	5.80 mm
Z (Stroke)	2 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	15 N
Pull-off force	15 N
Volume	0.50 cm ³
Curve radius (min) (convex)	20 mm
Size	20
Nipple family	SC030
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A
Weight	1.50 g

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Flat suction cup (round)

SUF 20 SI-CO-55 SC030

Part no.:10.01.01.14037

<https://www.schmalz.com/10.01.01.14037>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 030 G1/8-AG

Part no.:10.01.06.04288

Connection geometry: 030

Vacuum connection: G1/8"-M

Fitting length: 6 mm

Nominal diameter dn: 3.1 mm



SC 030 G1/8-IG

Part no.:10.01.06.04307

Connection geometry: 030

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 3.1 mm

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch