

Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

Part no.:10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 49-38 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 49 mm

Internal diameter d: 38 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 104 mm

Pressure range (operating pressure): -1.00 ... 4.47 bar

Operating temperature: -20 ... 90 °C

Design Data



Attribute	Value
d	38 mm
D	49 mm

Technical Data

Attribute	Value
Hose type	49-38
Pressure range (operating pressure)	-1.00 ... 4.47 bar
Operating temperature	-20 ... 90 °C
Bending radius min.	104 mm
Length max.	15 m
Weight/Meter	790 g/m
Weight/Meter	0.79 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

Part no.:10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 43-48 ST-VZ

Part no.:10.07.10.00020

Clamping range: 43.0 ... 48.0 mm

Material: Steel

Surface: galvanised



SSD 45-50 ST-VZ

Part no.:10.07.10.00157

Clamping range: 45.0 ... 50.0 mm

Material: Steel

Surface: galvanised



ST G1-1/2-AG 38 MS-V

Part no.:10.08.03.00170

Thread G1: G1-1/2"-M

Hose diameter (rec.) d: 38 mm

Material: Brass

Surface: nickel plated

Length L: 12.2 mm

Nominal diameter dn: 29.9 mm

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Vacuum hose (meter)

VSL 49-38 PU-DS-AS TR

Part no...:10.07.09.00052

<https://www.schmalz.com/10.07.09.00052>
