

## Flat suction cup (round)

SAF 30 NBR-60 RA

Part no.:10.01.01.10790

<https://www.schmalz.com/10.01.01.10790>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAF > SAF 30 NBR-60 RA

### Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 30


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: RA

### Design Data



| Attribute  | Value    |
|------------|----------|
| dn         | 4 mm     |
| Dmax(S)    | 34 mm    |
| Ds         | 31 mm    |
| H          | 23.20 mm |
| L4         | 31.80 mm |
| SW1        | 17 mm    |
| Z (Stroke) | 3 mm     |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                    | Value                |
|------------------------------|----------------------|
| Suction force (-600mbar)     | 38 N                 |
| Lateral force                | 30 N                 |
| Lateral force (oily surface) | 28 N                 |
| Volume                       | 2.72 cm <sup>3</sup> |
| Curve radius (min) (convex)  | 40 mm                |
| Hose diameter (rec.) d       | 4 mm                 |
| Size                         | 30                   |

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Flat suction cup (round)

SAF 30 NBR-60 RA

Part no.:10.01.01.10790

<https://www.schmalz.com/10.01.01.10790>

|                             |                    |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 60 Shore A         |
| Weight                      | 25.30 g            |
| Number of folds             | 0                  |
| Product family              | SAF                |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SU 30

Part no.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C