

Bellows suction cups (round)

FSG 7 HT1-60 G1/8-IG

Part no...:10.01.06.01243

<https://www.schmalz.com/10.01.06.01243>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 7 HT1-60 G1/8-IG

Bellows suction cup (round) for very uneven workpieces



Size: 7

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/8"-F

Number of folds: 2.5

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
d2	1.80 mm
dn	3.50 mm
Dmax(S)	7 mm
Ds	5.90 mm
G1	G1/8"-F
H	26 mm
LG1	8.50 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	7
Number of folds	2.50
Connection	G1/8-IG
Curve radius (min) (convex)	7.50 mm
Volume	0.04 cm ³

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

FSG 7 HT1-60 G1/8-IG

Part no.:10.01.06.01243

<https://www.schmalz.com/10.01.06.01243>

Suction force (-600mbar)	0.15 N
Pull-off force	0.90 N
Hose diameter (rec.) d	4 mm
Weight	4.70 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-IG DN350

Part no.:10.01.06.05731

Nipple family: N 016
Thread G1: G1/8"-F
Length L1: 18.5 mm
Fitting length: 12 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum



FG 7 HT1-60 N016

Part no.:10.01.06.01251

Size: 7
Suction cup material: High temperature material HT1
Material hardness [Shore A]: 60 Shore A
Number of folds: 2.5