

Flat suction cup (round)

SUF 90 SI-55 G1/4-AG

Part no.: 10.01.01.14070

<https://www.schmalz.com/10.01.01.14070>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 90 SI-55 G1/4-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 90


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
Dmax(S)	98.10 mm
Ds	90 mm
dn	5.10 mm
G1	G1/4"-M
H	23.20 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	7 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	328 N
Pull-off force	328 N
Volume	34.30 cm ³
Curve radius (min) (convex)	150 mm
Hose diameter (rec.) d	6 mm
Size	90
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Flat suction cup (round)

SUF 90 SI-55 G1/4-AG

Part no.:10.01.01.14070

<https://www.schmalz.com/10.01.01.14070>

Weight	98.10 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m