

Sealing profile (meter)

DI-PROF 6x8 MOS NK-20 HR

Part no.:10.07.04.00014

<https://www.schmalz.com/10.07.04.00014>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 6x8 MOS NK-20 HR

Sealing section for construction of specific gripper solutions



Width B: 6 mm

Height H: 8 mm


Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Form: half-round

Design Data



Attribute	Value
B	6 mm
H	8 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Natural Rubber NK
Recommended slot width x slot depth [mm]	7 x 4
Weight	33 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Sealing profile (meter)

DI-PROF 6x8 MOS NK-20 HR

Part no...:10.07.04.00014

<https://www.schmalz.com/10.07.04.00014>
