Bellows suction cup SI-MD (round)

FGA 25 SI-MD-55 N016

Part no..:10.01.06.04153

https://www.schmalz.com/10.01.06.04153


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > FGA 25 SI-MD-55 N016

Bellows suction cup (round) with optimal adaptation to uneven surfaces



- Size: 25
- Suction cup material: Silicone SI metal detectable
- Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	4.50 mm
d2	9.90 mm
Dk	10 mm
Dmax(S)	26.50 mm
Ds	22.50 mm
D1	25 mm
H	23 mm
H2	3.80 mm
H3	8.90 mm
Z (Stroke)	8.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1.50
Size	25
Suction cup material	Silicone SI metal detectable
Suction force (-600mbar)	5.30 N
Product family	FGA

Bellows suction cup SI-MD (round)

FGA 25 SI-MD-55 N016

Part no..:10.01.06.04153

https://www.schmalz.com/10.01.06.04153

Accessories



SA-NIP N016 G1/8-AG DN310

Part no..:10.01.06.04062

Nipple family: N 016
Thread G1: G1/8"-M
Length L1: 20 mm
Fitting length: 6 mm
Nominal diameter dn: 3.1 mm
Spanner size SW2: 3 mm
Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

Part no..:10.01.06.04365

Nipple family: N 016
Thread G1: M5-M
Length L1: 16 mm
Fitting length: 5 mm
Nominal diameter dn: 2.5 mm
Spanner size SW2: 3 mm
Material: Aust. Stainless steel



SA-NIP N016 M5-IG DN310

Part no..:10.01.06.04689

Nipple family: N 016
Thread G1: M5-F
Length L1: 16 mm
Fitting length: 10 mm
Nominal diameter dn: 3.1 mm
Spanner size SW2: 3 mm
Material: Aust. Stainless steel

Bellows suction cup SI-MD (round)

FGA 25 SI-MD-55 N016

Part no..:10.01.06.04153

https://www.schmalz.com/10.01.06.04153



SA-NIP N016 G1/8-IG DN310

Part no..:10.01.06.04690

Nipple family: N 016
Thread G1: G1/8"-F
Length L1: 18.5 mm
Fitting length: 12 mm
Nominal diameter dn: 3.1 mm
Material: Aust. Stainless steel