

Feed ejector

SEC-60 A2

Part no.:10.02.01.01155

<https://www.schmalz.com/10.02.01.01155>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-60 A2

Powerful ejector for very porous parts




Nozzle size: 6 mm

Suction rate (max.): 12.9 m³/h

Material: Aust. Stainless steel

Design Data



Attribute	Value
D	32 mm
D1	12.50 mm
D2	12.50 mm
G2	M5-F
G3	M3-F
L	14 mm
L1	44 mm
LG3	5 mm
X1	25 mm

Technical Data

Attribute	Value
Max. vacuum	-245 mbar
Suction rate (max.)	215 l/min
Suction rate (max.)	12.90 m ³ /h
Air consumption suction	140 l/min
Air consumption suction	6.60 m ³ /h
Pressure range (operating pressure)	2.0 ... 5.0 bar
Operating temperature	°C
Material	Aust. Stainless steel
Weight	0.09 kg

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Feed ejector

SEC-60 A2

Part no...:10.02.01.01155

<https://www.schmalz.com/10.02.01.01155>

Max. vacuum	-7.23 inHg
Suction rate (max.)	7.59 cfm
Air consumption suction	4.94 cfm
Pressure range (operating pressure)	29.0 ... 72.5
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)