

Basic Ejector

SEG 07 HS

Part no.:10.02.01.00255

<https://www.schmalz.com/10.02.01.00255>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SEG > SEG 07 HS

Basic ejector with robust housing for universal use




Nozzle diameter: 0.7 mm

Shape: For high vacuum

Suction rate (max.): 14 l/min

Air consumption suction: 21 l/min

Design Data



Attribute	Value
B	16 mm
D	15 mm
G1	G1/8"-F
G2	G1/8"-F
G3	G1/8"-F
H	26 mm
L	52 mm
SW1	14 mm

Technical Data

Attribute	Value
Nozzle diameter	0.70 mm
Degree of evacuation	85 %
Suction rate (max.)	14 l/min
Suction rate (max.)	0.80 m³/h
Suction rate (max.)	0.49 cfm
Air consumption suction	21 l/min
Air consumption suction	1.30 m³/h
Air consumption suction	0.74 cfm
Pressure range (operating pressure)	3.0 ... 6.0 bar

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Basic Ejector

SEG 07 HS

Part no.:10.02.01.00255

<https://www.schmalz.com/10.02.01.00255>

Pressure range (operating pressure)	43.5 ... 87.0
Pressure optimal	5 bar
Pressure optimal	72.50 psi
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	4 mm
Operating temperature	-10 ... 80 °C
Weight	41 g
Product family	SEG

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



VFI CN6/4 50

Part no.:10.07.01.00241

Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm



VFI 4/2 50

Part no.:10.07.01.00329

Connection: Hose 4/2

Filter pore size: 50 µm

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Basic Ejector

SEG 07 HS

Part no...:10.02.01.00255

<https://www.schmalz.com/10.02.01.00255>



VFI CN8/6 50

Part no...:10.07.01.00245

Connection: Hose 8/6 with Cap nut

Filter pore size: 50 µm



VFI 6/4 50

Part no...:10.07.01.00328

Connection: Hose 6/4

Filter pore size: 50 µm



VS-V-W-D PNP K 3C-D

Part no...:10.06.02.00678

Measuring range: -1,0 ... 0,0 bar

Shape: Cube, digital display

Construction shape vacuum switch: PNP switching

Electrical connection: Cable

Inputs/outputs: 2 digital

Display: Display 3-color / 2-line

Protection type IP: IP 40

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Basic Ejector

SEG 07 HS

Part no...:10.02.01.00255

<https://www.schmalz.com/10.02.01.00255>



VS-P10-W-D PNP K 3C-D

Part no...:10.06.02.00680

Measuring range: 0,0 ... 10,0 bar

Shape: Cube, digital display

Construction shape vacuum switch: PNP switching

Electrical connection: Cable

Inputs/outputs: 2 digital

Display: Display 3-color / 2-line

Protection type IP: IP 40

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es