

Flat suction cup (round)

SAF 60 NBR-60 RA

Part no.:10.01.01.10799

<https://www.schmalz.com/10.01.01.10799>

Home > Flat Suction Cups SAF > SAF 60 NBR-60 RA

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 60


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: RA

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	67 mm
Ds	60.60 mm
H	30.70 mm
L4	31.80 mm
SW1	22 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	150 N
Lateral force	105 N
Lateral force (oily surface)	85 N
Volume	16.70 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	60
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SAF 60 NBR-60 RA

Part no...:10.01.01.10799

<https://www.schmalz.com/10.01.01.10799>

Material hardness [Shore A]	60 Shore A
Weight	46.50 g
Number of folds	0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 60

Part no...:10.01.01.13585

Size: 60

Clamping range: 60.0 ... 70.0 mm

Temperature resistance: 80 °C