

## Mounting profile

MO-PROF 40 3TN AL-1

Part no.: 26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Sections and Connectors > Mounting Profiles MO-PROF > MO-PROF 40 3TN AL-1

### Aluminium profile for construction of vacuum-gripping systems




Width B: 40 mm

Length max.: 6,000 mm

Form: with 3 T-slots

Material: Al Mg Si 0.5 F22

### Design Data



Note: Additional costs for cut

| Attribute     | Value    |
|---------------|----------|
| B             | 40 mm    |
| B1            | 20 mm    |
| B3            | 5.20 mm  |
| d             | 4.60 mm  |
| H1            | 20.50 mm |
| H2            | 10 mm    |
| Length (max.) | 6000 mm  |

### Technical Data

| Attribute            | Value                 |
|----------------------|-----------------------|
| Area                 | 6.50 cm <sup>2</sup>  |
| Resistance moment Wx | 5.50 cm <sup>3</sup>  |
| Resistance moment Wy | 5.20 cm <sup>3</sup>  |
| Area moment Ix       | 12.70 cm <sup>4</sup> |
| Area moment Iy       | 10.40 cm <sup>4</sup> |
| Warping max.         | 0.80 mm/m             |
| Material             | Al Mg Si 0.5 F22      |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)

## Mounting profile

MO-PROF 40 3TN AL-1


Part no.:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>

|                |           |
|----------------|-----------|
| Mass           | 1.80 kg/m |
| Product family | MO-PROF   |

Note: There are additional costs for cutting!

## Accessories



### BEF-WIN 40x40x40 5 MO-PROF

Part no.:25.09.06.00007

|                                    |
|------------------------------------|
| Width B: 40 mm                     |
| Height H: 40 mm                    |
| Length L: 40 mm                    |
| Wall thickness s: 5 mm             |
| Construction use: Mounting section |
| Weight: 107 g                      |



### DI-RA 40 PPTA MO-PROF

Part no.:10.07.08.00131

|                                    |
|------------------------------------|
| Height H: 1 mm                     |
| Length L: 40 mm                    |
| Wall thickness s: 10.5 mm          |
| Construction use: Mounting section |
| Weight: 2 g                        |

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)

## Mounting profile

MO-PROF 40 3TN AL-1

Part no...:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



### NUT-STEI 10x20 M6-IG

Part no...:25.09.06.00002

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 10 mm

Thread G1: M6-F

Shape mounting elements: With step

Surface: galvanised

Weight: 6 g



### NUT-STEI 10x20 M8-IG

Part no...:25.09.06.00003

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 10 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 5 g



### NUT-STEI 20x20 M8-IG 10

Part no...:25.09.06.00012

Width B: 20 mm

Height H: 4.9 mm

Material: Steel

Length L: 20 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 15.9 g

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)

## Mounting profile

MO-PROF 40 3TN AL-1

Part no.: 26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



### SCHR WN1552 5x20 ST VZ T25

Part no.: 20.10.03.00008

External diameter D: 5 mm

Material: Steel

Length L: 20 mm

Surface: galvanised

Weight: 3.9 g



### VBR-PR 150x3 E-FL


Part no.: 25.09.06.00006

Height H: 3 mm

Length L: 150 mm

Weight: 362 g

Connection 1: 2 Sliding blocks



### VBR-PR 185x185x3 K-FL

Part no.: 25.09.06.00005

Width B: 185 mm

Height H: 3 mm

Length L: 185 mm

Weight: 279 g

Connection 1: 2 sliding blocks

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)

## Mounting profile

MO-PROF 40 3TN AL-1

Part no...:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



### VBR-PR 40x55x55 E-V

Part no...:10.08.03.00099

Width B: 55 mm

Height H: 55 mm

Length L: 40 mm

Wall thickness s: 6 mm

Weight: 164 g



### VRS-PL-40 G1/2-IG MO-PROF

Part no...:25.09.06.00009

Height H: 10 mm

Length L: 40 mm

Thread G1: G1/2"-F

Construction use: Mounting section

Weight: 72 g



### VRS-PL-40 MO-PROF

Part no...:25.09.06.00026

Height H: 5 mm

Material: Polyamide

Length L: 40 mm

Construction use: Mounting section

Weight: 11.1 g

## Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)

## Mounting profile

MO-PROF 40 3TN AL-1

Part no.:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



### VRS-PL-40 MO-PROF

Part no.:25.09.06.00008

Height H: 4 mm

Material: Steel

Length L: 40 mm

Construction use: Mounting section

Weight: 45 g

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | [kundencenter@schmalz.de](mailto:kundencenter@schmalz.de)