

Flat suction cup (round)

SPF 60 ED-65 SC050

Part no.:10.01.01.12896

<https://www.schmalz.com/10.01.01.12896>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPF 60 ED-65 SC050

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 60

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 18.1 mm

Design Data



Attribute	Value
d	10.50 mm
d1	17.50 mm
Dk	22.10 mm
Dmax(S)	65 mm
Ds	61.20 mm
H	18.10 mm
H2	7.50 mm
Z (Stroke)	5.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	107 N
Pull-off force	135 N
Lateral force	65 N
Volume	12.67 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	60

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SPF 60 ED-65 SC050

Part no.:10.01.01.12896

<https://www.schmalz.com/10.01.01.12896>

Nipple family	SC 050
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	9 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 050-AR NPT1/4-AG MOD

Part no.:10.01.06.02543

Connection geometry: 050-AR

Connection: NPT1/4-M

Length L1: 29 mm

Fitting length: 7.5 mm

Nominal diameter dn: 6.1 mm



SC 050-AR NPT1/4-IG MOD

Part no.:10.01.06.02546

Connection geometry: 050-AR

Connection: NPT1/4-F

Length L1: 28.5 mm

Fitting length: 19.2 mm

Nominal diameter dn: 6.1 mm

Flat suction cup (round)

SPF 60 ED-65 SC050

Part no...:10.01.01.12896

<https://www.schmalz.com/10.01.01.12896>



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Part no...:10.07.01.00308

External diameter D: 17.5 mm

Length L: 0.8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm