

Bellows suction cup (rectangular)


FSGB-R 52x25 SI-50 G1/8-IG

Part no.:10.01.06.02288

<https://www.schmalz.com/10.01.06.02288>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups FSGB-R (Rectangular) > FSGB-R 52x25 SI-50 G1/8-IG

Bellows suction cup (rectangular)



Dimensions (LxB): 52 x 25

Suction cup material: Silicone SI


Material hardness [Shore A]: 50 Shore A

Nipple material: Aluminum

Connection: G1/8-IG

Number of folds: 2.5

Design Data



Attribute	Value
b2	10 mm
B1	25 mm
Bmax(S)	27.50 mm
Bs	25 mm
G1	G1/8"-F
H	32 mm
I2	37 mm
L1	52 mm
LG1	6 mm
Lmax(S)	54.50 mm
Ls	52 mm
Z (Stroke)	15 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3 The specified stroke is for use with a supporting frame in each fold

Technical Data

Attribute	Value
Suction force (-600mbar)	20 N
Volume	16 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	6 mm

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Bellows suction cup (rectangular)

FSGB-R 52x25 SI-50 G1/8-IG

Part no.:10.01.06.02288

<https://www.schmalz.com/10.01.06.02288>

Dimensions (LxB)	52 x 25
Number of folds	2.50
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A
Weight	34 g
Product family	FSGB-R

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories




ST-RAHM 50x23 1

Part no.:10.01.06.02276

Length L: 50 mm

Width B: 23 mm

Spare parts



FGB-R 52x25 SI-50

Part no.:10.01.06.01116

Dimensions (LxB): 52 x 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A

Number of folds: 2.5