Bellows suction cups (round)

FSG 12 NBR-ESD-55 M5-AG

Part no..:10.01.06.04342

https://www.schmalz.com/10.01.06.04342

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 12 NBR-ESD-55 M5-AG

Bellows suction cup (round) for very uneven workpieces

- Size: 12
- Suction cup material: Nitrile rubber NBR-ESD
- Material hardness [Shore A]: 55 Shore A
- Nipple material: Aluminum
- Connection: M5-M
- Number of folds: 2.5
- Vacuum connection: M5-M

Design Data



Attribute	Value
d2	5 mm
dn	2.50 mm
Dmax(S)	13 mm
Ds	12 mm
G1	M5-M
H	26 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Size	12
Number of folds	2.50
Connection	M5-AG
Curve radius (min) (convex)	12.50 mm
Volume	0.60 cm^3

Bellows suction cups (round)

FSG 12 NBR-ESD-55 M5-AG

Part no..:10.01.06.04342

https://www.schmalz.com/10.01.06.04342

Suction force (-600mbar)	1.18 N
Pull-off force	3.50 N
Hose diameter (rec.) d	2 mm
Weight	2.20 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts

FG 12 NBR-ESD-55 N062

Part no..:10.01.06.04260

Size: 12
Suction cup material: Nitrile rubber NBR-ESD
Material hardness [Shore A]: 55 Shore A
Number of folds: 2.5

SA-NIP N062 M5-AG DN250

Part no..:10.01.06.05668

Thread G1: M5-M
Length L1: 15.9 mm
Fitting length: 5 mm
Nominal diameter dn: 2.5 mm
Material: Aluminum