

Vacuum centre

VZ-TR 25 AC3 50 MS

Part no...:10.03.04.00142

<https://www.schmalz.com/10.03.04.00142>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Centers > Vacuum Centers VZ > VZ-TR 25 AC3 50 MS

Vacuum centre with oil-free pump and vacuum reservoir




Suction rate: 25 m³/h

Voltage: 230/400V ±10%

Reservoirs volume: 50 l

with: Motor-protection switch

Design Data



Attribute	Value
B	510 mm
B1	630 mm
d	11 mm
G2	G1-1/4"-F
H	580 mm
L	710 mm
L1	730 mm
X1	480 mm
Y1	470 mm

Technical Data

Attribute	Value
Max. vacuum	-850 mbar
Voltage	230/400V ±10%
Motor power	0.75 kW
Reservoirs volume	50 l
Suction rate	25 m ³ /h
Protection type IP	
Weight	70 kg
Max. vacuum	-25.10 inHg

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 2
schmalz@schmalz.co.uk

Vacuum centre

VZ-TR 25 AC3 50 MS

Part no.:10.03.04.00142

<https://www.schmalz.com/10.03.04.00142>

Product family

VZ

Spare parts



FILT-EINS EVE-TR-25-40

Part no.:10.03.01.00023

Size: 25-40

Construction use: Pump EVE-TR



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no.:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 2
schmalz@schmalz.co.uk