

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2

Part no.:10.03.01.00349

<https://www.schmalz.com/10.03.01.00349>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices VacuMaster > Spare Parts VacuMaster Basic / Comfort > EVE-TR 25 AC3 IE3-TYP2

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Voltage at 60Hz: YY230/Y460V ±10%

Suction rate (60 Hz): 30 m³/h


Rated power 60 Hz: 0.9 kW

Construction: IE3:US/CAN

Permission: UL/CSA

Weight: 27.5 kg

Design Data



Attribute	Value
B	270 mm
B2	50 mm
d	7 mm
G3	G3/4"-F
H	292 mm
L	465 mm
L2	96 mm
X1	220 mm
Y1	190 mm

Technical Data

Attribute	Value
Suction rate (60 Hz)	30 m³/h
Voltage at 60Hz	YY230/Y460V ±10%
Rated power 60 Hz	0.90 kW
Current type	AC3
Current type	three-phase current
Construction	IE3:US/CAN
Weight	27.50 kg
Protection type IP	IP 55

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2

Part no...:10.03.01.00349

<https://www.schmalz.com/10.03.01.00349>

Product family

EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



VBV -950...0 G1-AG EVE 10-40

Part no...:10.03.01.00136

External diameter D: 46 mm

Max. vacuum: -950 mbar

Thread G1: G1"-M

Length L: 53.5 mm

Construction use: Pump EVE

Size: 10-40



VOL 50

Part no...:10.03.03.00118

Reservoirs volume: 50 l

Height H: 235 mm

Add. function: Manometer, valve, filter

Spare parts

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum pump

EVE-TR 25 AC3 IE3-TYP2

Part no...:10.03.01.00349

<https://www.schmalz.com/10.03.01.00349>



VST EVE-TR-25

Part no...:10.03.01.00134

Construction use: Pump EVE-TR

Size: 25

contains: Brush slide

and: Filter



FILT-EINS 3 65x70 PAP STF-3/4-IG

Part no...:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69.5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG