

Flat suction cup (round)

PFYN 6 SI-CO-55 M5-AG

Part no.:10.01.01.10394

<https://www.schmalz.com/10.01.01.10394>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 6 SI-CO-55 M5-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 6


Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: M5-M

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	6.50 mm
Ds	6 mm
G1	M5-M
H	11.50 mm
LG1	4.50 mm
SW1	8 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1.20 N
Volume	0.01 cm ³
Curve radius (min) (convex)	7.50 mm
Hose diameter (rec.) d	2 mm
Size	6
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Flat suction cup (round)

PFYN 6 SI-CO-55 M5-AG

Part no.:10.01.01.10394

<https://www.schmalz.com/10.01.01.10394>

Weight 1.10 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N004 M5-AG DN200

Part no.:10.01.01.03526

Thread G1: M5-M

Length L1: 13.5 mm

Fitting length: 5 mm

Material: Aluminum



PFG 6 SI-CO-55 N004

Part no.:10.01.01.00626

Size: 6

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A