

## Multi-Clamp

VC-M 165x165x220.5

Part no...:10.01.12.01845

<https://www.schmalz.com/10.01.12.01845>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp System VC-M / VC-M-V > VC-M 165x165x220.5

### Vacuum clamping system Multi-Clamp with integrated vacuum generation



Length L: 165 mm

Width B: 165 mm


Height H: 220.5 mm

Air consumption: 48 l/min

Air consumption: 2.88 m³/h

Suction rate: 2.3 m³/h

### Design Data



| Attribute | Value     |
|-----------|-----------|
| B         | 165 mm    |
| H         | 220.50 mm |
| L         | 165 mm    |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 5.76 kg |

### Accessories

#### Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)

## Multi-Clamp

VC-M 165x165x220.5

Part no...:10.01.12.01845

<https://www.schmalz.com/10.01.12.01845>



**DI-PROF 8x10.5 MOS EPDM-15**

Part no...:10.01.12.02056



**REIB-INS 8.1x18 VC-M**

Part no...:10.01.12.02000

Construction use: Multi-Clamp



**VC-M-SP 160x160x30**

Part no...:10.01.12.01836

Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Air consumption: 48 l/min

Air consumption: 2.88 m³/h

Suction rate: 2.3 m³/h

### Contact Schmalz


Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)

## Multi-Clamp

VC-M 165x165x220.5

Part no...:10.01.12.01845

<https://www.schmalz.com/10.01.12.01845>



### VC-M-SP 200x55

Part no...:10.01.12.02003

Length L: 200 mm

Width B: 55 mm

Air consumption: 48 l/min

Air consumption: 2.88 m<sup>3</sup>/h

Suction rate: 2.3 m<sup>3</sup>/h



### VC-M-SP 210

Part no...:10.01.12.02002

External diameter D: 210 mm

Air consumption: 48 l/min

Air consumption: 2.88 m<sup>3</sup>/h

Suction rate: 2.3 m<sup>3</sup>/h



### VC-M-SP 300x100

Part no...:10.01.12.02052

Length L: 300 mm

Width B: 100 mm

Air consumption: 48 l/min

Air consumption: 2.88 m<sup>3</sup>/h

Suction rate: 2.3 m<sup>3</sup>/h

## Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)