

## Clamping piece with extension

SXT-CL-EXT-A2-125-F40

Part no.:10.07.13.00082

<https://www.schmalz.com/10.07.13.00082>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Tooling System SXT > Clamping Pieces with Extension  
SXT-CL-EXT > SXT-CL-EXT-A2-125-F40

### Swivel arm with extension to connect Vacuum-Components with Round Toolings



External diameter D: 40 mm


Internal diameter d: 19 mm

Hole spacing X1: 126 mm

Material: Aluminum

Connection 1: Bolt with slot Ø19mm

### Design Data



| Attribute | Value     |
|-----------|-----------|
| B         | 25 mm     |
| D         | 40 mm     |
| d         | 19 mm     |
| H1        | 83 mm     |
| H2        | 25.50 mm  |
| H3        | 12.50 mm  |
| L         | 171.50 mm |
| L1        | 179.50 mm |
| L2        | 75 mm     |
| X1        | 126 mm    |

### Technical Data

| Attribute      | Value    |
|----------------|----------|
| Material       | Aluminum |
| Shape          | Female   |
| Weight         | 320 g    |
| Product family | SXT      |

### Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 1  
schmalz@schmalz.co.uk