

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Part no.:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAXM > SAXM 115 ED-85 M14x1.5-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 115

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: M14x1.5-AG

Design Data



Attribute	Value
dn	6.10 mm
Dmax(S)	129.40 mm
Ds	115.20 mm
G1	M14x1.5-M
H	50.10 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	549 N
Lateral force	320 N
Lateral force (oily surface)	584 N
Volume	141.50 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	115

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 3
schmalz@schmalz.co.uk

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Part no.:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>

Connection	M14x1.5-M
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	92.50 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC-A 065 M14x1.5-AG L

Part no.:10.01.06.02826

Connection geometry: 065

Thread G1: M14x1.5-M

Fitting length: 8 mm

Shape: Self Locking



SAXM 115 ED-85 SC065

Part no.:10.01.19.00010

Size: 115

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 3
schmalz@schmalz.co.uk

Bell suction cup (round)

SAXM 115 ED-85 M14x1.5-AG

Part no...:10.01.19.00047

<https://www.schmalz.com/10.01.19.00047>



SC-S 065 FDC-L

Part no...:10.01.06.02805

Shape: Frict elem with Self lock

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 3 from 3
schmalz@schmalz.co.uk