

Flat suction cup (round)

PFYN 50 NBR-CO-55 G1/8-AG

Part no.:10.01.01.10390

<https://www.schmalz.com/10.01.01.10390>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 50 NBR-CO-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 50


Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2.40 mm
Dmax(S)	53.50 mm
Ds	50 mm
G1	G1/8"-M
H	20 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	91 N
Volume	7 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	4 mm
Size	50
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (round)

PFYN 50 NBR-CO-55 G1/8-AG

Part no.:10.01.01.10390

<https://www.schmalz.com/10.01.01.10390>

Weight 15.30 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 50

Part no.:10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N008 G1/8-AG DN350

Part no.:10.01.01.03532

Thread G1: G1/8"-M

Length L1: 22 mm

Fitting length: 5 mm

Material: Aluminum

Spanner size SW2: 4 mm

Flat suction cup (round)

PFYN 50 NBR-CO-55 G1/8-AG

Part no...:10.01.01.10390

<https://www.schmalz.com/10.01.01.10390>



PFG 50 NBR-CO-55 N008

Part no...:10.01.01.10342

Size: 50

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A