

Flat suction cup (oval)

SAOF 100x50 NBR-60 G1/4-IG

Part no.:10.01.05.00281

<https://www.schmalz.com/10.01.05.00281>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 100x50 NBR-60 G1/4-IG

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 100x50

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G1/4-IG

Design Data



Attribute	Value
Bmax(S)	54 mm
Bs	48.10 mm
dn	8 mm
G1	G1/4"-F
H	30 mm
LG1	8 mm
Lmax(S)	106 mm
Ls	101.10 mm
SW1	17 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	217 N
Lateral force	181 N
Lateral force (oily surface)	121 N
Volume	21.80 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Number of folds	0

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 2
schmalz@schmalz.co.uk

Flat suction cup (oval)

SAOF 100x50 NBR-60 G1/4-IG

Part no...:10.01.05.00281

<https://www.schmalz.com/10.01.05.00281>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	73 g
Product family	SAOF
Dimensions (LxB)	100x50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 2
schmalz@schmalz.co.uk