

Flat suction cup (oval)

SAOF 90x30 NBR-45 M10-AG

Part no.:10.01.05.00572

<https://www.schmalz.com/10.01.05.00572>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 90x30 NBR-45 M10-AG

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 90x30

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 45 Shore A

Nipple material: Steel

Connection: M10-AG

Design Data



Attribute	Value
Bmax(S)	34 mm
Bs	30.60 mm
dn	4 mm
G1	M10-M
H	19 mm
LG1	10 mm
Lmax(S)	94 mm
Ls	90.60 mm
SW1	17 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	122 N
Lateral force	96 N
Lateral force (oily surface)	64 N
Volume	10.10 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Number of folds	0

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Flat suction cup (oval)

SAOF 90x30 NBR-45 M10-AG

Part no...:10.01.05.00572

<https://www.schmalz.com/10.01.05.00572>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45 Shore A
Weight	51 g
Product family	SAOF
Dimensions (LxB)	90x30

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m