

Flat suction cup (round)

SUF 100 HT1-60 G1/4-AG

Part no.:10.01.01.14081

<https://www.schmalz.com/10.01.01.14081>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 100 HT1-60 G1/4-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 100

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
Dmax(S)	108 mm
Ds	100 mm
dn	5.10 mm
G1	G1/4"-M
H	24 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	7.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	402 N
Pull-off force	402 N
Volume	46.40 cm ³
Curve radius (min) (convex)	200 mm
Hose diameter (rec.) d	6 mm
Size	100
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (round)

SUF 100 HT1-60 G1/4-AG

Part no.:10.01.01.14081

<https://www.schmalz.com/10.01.01.14081>

Weight	112.10 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m