

Vacuum pump

EVE-OG 100 AC3 F IE3

Part no...:10.03.02.00066

<https://www.schmalz.com/10.03.02.00066>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 100 AC3 F IE3

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Suction rate (60 Hz): 120 m³/h

Permission: IE3

Rated power 60 Hz: 3.4 kW

Current type: three-phase current

Sound level at 50 Hz: 65 dB(A)


with: Filter

Suction rate (50 Hz): 100 m³/h

Rated power 50 Hz: 2.7 kW

Weight: 76.5 kg

Design Data



Attribute	Value
B	406 mm
B2	14.80 mm
G2	G1-1/4"-F
G3	G1-1/4"-F
H	290 mm
H1	414 mm
H2	75 mm
L	692 mm
L2	170 mm
X1	226 mm
Y1	277 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	100 m³/h
Rated power 50 Hz	2.70 kW
Sound level at 50 Hz	65 dB(A)
Weight	76.50 kg

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Vacuum pump

EVE-OG 100 AC3 F IE3

Part no...:10.03.02.00066

<https://www.schmalz.com/10.03.02.00066>

Protection type IP	IP 55
Current type	AC3
Product family	EVE-OG

Accessories



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG



ZUB EVE-OG Ölablass-Kit

Part no...:22.09.03.00038

Construction use: Pump EVE-OG

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in