

## Flat suction cup (oval)

SAOF 140x70 NBR-60 G1/4-IG

Part no.:10.01.05.00287

<https://www.schmalz.com/10.01.05.00287>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 140x70 NBR-60 G1/4-IG

### Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 140x70


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G1/4-IG

### Design Data



| Attribute  | Value     |
|------------|-----------|
| Bmax(S)    | 76 mm     |
| Bs         | 67.60 mm  |
| dn         | 8 mm      |
| G1         | G1/4"-F   |
| H          | 33 mm     |
| LG1        | 8 mm      |
| Lmax(S)    | 149 mm    |
| Ls         | 140.60 mm |
| SW1        | 17 mm     |
| Z (Stroke) | 7 mm      |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                    | Value                 |
|------------------------------|-----------------------|
| Suction force (-600mbar)     | 425 N                 |
| Lateral force                | 344 N                 |
| Lateral force (oily surface) | 230 N                 |
| Volume                       | 57.30 cm <sup>3</sup> |
| Curve radius (min) (convex)  | 90 mm                 |
| Hose diameter (rec.) d       | 6 mm                  |
| Number of folds              | 0                     |

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Flat suction cup (oval)

SAOF 140x70 NBR-60 G1/4-IG

Part no...:10.01.05.00287

<https://www.schmalz.com/10.01.05.00287>

|                             |                    |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 60 Shore A         |
| Weight                      | 95 g               |
| Product family              | SAOF               |
| Dimensions (LxB)            | 140x70             |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m