

Flexolink

FLK G1/4-IG M10x1.25-AG

Part no...:10.01.03.00206

<https://www.schmalz.com/10.01.03.00206>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/4-IG M10x1.25-AG

Flexible suction cup mounting for adaptation to sloping surfaces




Thread G1: G1/4"-F

Thread G2: M10x1.25-M

Operating temperature: 0 ... 70 °C

Design Data



Attribute	Value
dn	2.80 mm
G1	G1/4"-F
G2	M10x1.25-M
L	32 mm
LG1	10.50 mm
LG2	8 mm
SW1	17 mm
W	12 °

Technical Data

Attribute	Value
Bending moment	8 Nm
Vertical load	500 N
Weight	26 g
Product family	FLK

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it