

## Flat suction cup (round)

SAF 40 NBR-60 G1/4-AG

Part no.:10.01.01.10647

<https://www.schmalz.com/10.01.01.10647>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAF > SAF 40 NBR-60 G1/4-AG

### Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 40


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

### Design Data



| Attribute  | Value   |
|------------|---------|
| dn         | 4 mm    |
| Dmax(S)    | 46 mm   |
| Ds         | 41 mm   |
| G1         | G1/4"-M |
| H          | 22 mm   |
| LG1        | 10 mm   |
| SW1        | 17 mm   |
| Z (Stroke) | 4 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                    | Value                |
|------------------------------|----------------------|
| Suction force (-600mbar)     | 69 N                 |
| Lateral force                | 52 N                 |
| Lateral force (oily surface) | 50 N                 |
| Volume                       | 5.30 cm <sup>3</sup> |
| Curve radius (min) (convex)  | 50 mm                |
| Hose diameter (rec.) d       | 4 mm                 |
| Size                         | 40                   |

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Flat suction cup (round)

SAF 40 NBR-60 G1/4-AG

Part no.:10.01.01.10647

<https://www.schmalz.com/10.01.01.10647>

|                             |                    |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 60 Shore A         |
| Weight                      | 18.90 g            |
| Number of folds             | 0                  |
| Product family              | SAF                |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C