

Mechanical clamp

VCMC-K2-QUICK 170x135x100 10-100

Part no.:10.01.12.04613

<https://www.schmalz.com/10.01.12.04613>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Narrow Workpieces > Mechanical Clamps VCMC-K2-QUICK > VCMC-K2-QUICK 170x135x100 10-100

Mechanical clamp for narrow and frame parts, 2-circuit console



Shape: QUICK

Dimensions (LxB): 170x135


Height H: 100 mm

Stroke Z: 10 mm

Clamping range: 10.0 ... 100.0 mm

Add. function: Toolless height adjustment

Design Data



Attribute	Value
B	133.30 mm
D1	56 mm
H	100 mm
H1	233.50 mm
H2	30 mm
L	170 mm
X1	66.50 mm
X2	44 mm

Technical Data

Attribute	Value
Clamping range	10.0 ... 100.0 mm

Accessories

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Mechanical clamp

VCMC-K2-QUICK 170x135x100 10-100

Part no...:10.01.12.04613

<https://www.schmalz.com/10.01.12.04613>



KLEM-EINH 70x24.5x4.5 VCMC-K2

Part no...:10.01.12.04255

Height H: 4.5 mm

Construction use: Mechanical clamp VCMC-K2



KLEM-EINH 69.5x35x12.5

Part no...:10.01.12.04990

Length L: 69.5 mm

Width B: 35 mm

Height H: 12.5 mm



ZUB VCMC-K2

Part no...:10.01.12.04611

Construction use: Mechanical clamp VCMC-K2

Spare parts

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Mechanical clamp

VCMC-K2-QUICK 170x135x100 10-100

Part no...:10.01.12.04613

<https://www.schmalz.com/10.01.12.04613>




SPAN-TELL 110 EXZ VCMC

Part no...:10.01.12.04239

External diameter D: 110 mm

Installation position: EXZ

Construction use: Mechanical clamp VCMC



VCDR 166x113x6.6 VCSP

Part no...:10.01.12.02191


Length L: 166 mm

Width B: 113 mm

Height H: 6.6 mm

Construction use: Suction plate vacuum block

Clamping range: mm



VCDR 166x113x6.6 VCSP

Part no...:10.01.12.02191

Length L: 166 mm

Width B: 113 mm

Height H: 6.6 mm

Construction use: Suction plate vacuum block

Clamping range: mm