

Bellows suction cup (oval)

SAOB 60x30 NBR-60 G1/4-IG

Part no.:10.01.06.00891

<https://www.schmalz.com/10.01.06.00891>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows Suction Cups SAOB HT2 (Oval, 1.5 Folds) > SAOB 60x30 NBR-60 G1/4-IG

Bellows suction cup (oval) for high dynamic on curved, oily surfaced workpieces



Dimensions (LxB): 60 x 30

Suction cup material: Nitrile rubber NBR


Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
B1	31 mm
Bmax(S)	33 mm
Bs	30.60 mm
dn	5.50 mm
G1	G1/4"-F
H	34.50 mm
L1	55.70 mm
LG1	8 mm
Lmax(S)	63 mm
Ls	60.60 mm
SW1	17 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	38 N
Pull-off force	69.50 N
Lateral force	72.50 N
Lateral force (oily surface)	41.70 N
Volume	10.50 cm ³

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Bellows suction cup (oval)

SAOB 60x30 NBR-60 G1/4-IG

Part no.:10.01.06.00891

<https://www.schmalz.com/10.01.06.00891>

Curve radius (min) (convex)	18 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	60 x 30
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Number of folds	1.50
Weight	35.40 g
Product family	SAOB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr