

Friction ring

REIB-RING SGM 30 HT2-65

Part no.:10.01.17.00410

<https://www.schmalz.com/10.01.17.00410>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > REIB-RING SGM 30 HT2-65

Friction ring




Construction use: Magnetic gripper

Size: 30

External diameter D: 29.5 mm

Internal diameter d: 20.5 mm

Design Data



Attribute	Value
D	29.50 mm
L	10.70 mm

Technical Data

Attribute	Value
Size	30
Suction cup material	High temperature material HT2
Operating temperature (max.)	200 °C
Material hardness [Shore A]	65 Shore A
Weight	3 g

Operating temperature max. short-term up to +250 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr



Friction ring

REIB-RING SGM 30 HT2-65

Part no.:10.01.17.00410

<https://www.schmalz.com/10.01.17.00410>

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr