Friction ring

REIB-RING SGM 50 HT2-65

Part no..:10.01.17.00412

https://www.schmalz.com/10.01.17.00412


Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > REIB-RING SGM 50 HT2-65

Friction ring



Construction use: Magnetic gripper
Size: 50
External diameter D: 50 mm
Internal diameter d: 41.5 mm

Design Data



Attribute	Value
D	50 mm
L	10.70 mm

Technical Data

Attribute	Value
Size	50
Suction cup material	High temperature material HT2
Operating temperature (max.)	200 °C
Material hardness [Shore A]	65 Shore A
Weight	4.70 g

Operating temperature max. short-term up to +250 °C

Contact Schmalz
Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2403
schmalz@schmalz.co.kr

Friction ring

REIB-RING SGM 50 HT2-65

Part no..:10.01.17.00412

https://www.schmalz.com/10.01.17.00412

Contact Schmalz
Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8776 2431
schmalz@schmalz.co.kr