

Inline ejector

VR 09

Part no.:10.02.01.00077

<https://www.schmalz.com/10.02.01.00077>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Inline Ejectors > Inline Ejectors VR > VR 09

Inline ejector for vacuum generation directly at the suction cup



Nozzle diameter: 0.9 mm


Degree of evacuation: 89 %

Suction rate (max.): 21 l/min

Air consumption suction: 36 l/min

Pressure optimal: 5 bar

Design Data



Attribute	Value
G2	G1/8"-F
G3	M5-M
H1	29.80 mm
H2	4 mm
L	35 mm
L2	16 mm
LG3	5 mm
SW1	17 mm
G1	G1/4"-F

Technical Data

Attribute	Value
Nozzle diameter	0.90 mm
Degree of evacuation	89 %
Suction rate (max.)	21 l/min
Suction rate (max.)	1.30 m³/h
Air consumption suction	36 l/min
Air consumption suction	2.20 m³/h
Pressure optimal	5 bar
Operating temperature	0 ... 60 °C
Weight	15 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Inline ejector

VR 09

Part no...:10.02.01.00077

<https://www.schmalz.com/10.02.01.00077>

Suction rate (max.)	0.74 cfm
Air consumption suction	1.27 cfm
Pressure optimal	72.50 psi
Product family	VR

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it