

Suction cup connection nipple

SA-NIP N008 G1/8-IG DN350

Part no.:10.01.01.03524

<https://www.schmalz.com/10.01.01.03524>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SA-NIP N008 G1/8-IG DN350

Suction cup connection nipple



Thread G1: G1/8"-F


Length L1: 25 mm

Fitting length: 16 mm

Material: Aluminum

Spanner size SW2: 4 mm

Design Data



Attribute	Value
D	14 mm
dn	3.50 mm
D2	8.50 mm
G1	G1/8"-F
L	16 mm
L1	25 mm
L2	7 mm
L3	2 mm
LG1	9 mm
SW1	14 mm
SW2	4 mm

Technical Data

Attribute	Value
Nipple family	N 008
Material	Aluminum
Weight	6.70 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction cup connection nipple

SA-NIP N008 G1/8-IG DN350

Part no.:10.01.01.03524

<https://www.schmalz.com/10.01.01.03524>

Accessories



PFG 50 FPM-65 N008

Part no.:10.01.01.00077

Size: 50

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 50 HT1-60 N008

Part no.:10.01.01.11168

Size: 50

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 50 NBR-CO-55 N008

Part no.:10.01.01.10342

Size: 50

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction cup connection nipple

SA-NIP N008 G1/8-IG DN350

Part no...:10.01.01.03524

<https://www.schmalz.com/10.01.01.03524>



PFG 50 NBR-55 N008

Part no...:10.01.01.00017

Size: 50

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 50 PU-55 N008

Part no...:10.01.01.00057

Size: 50

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 50 SI-55 N008

Part no...:10.01.01.00037

Size: 50

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible