

Flat suction cup (round)

PFYN 30 NBR-ESD-55 G1/8-AG

Part no.:10.01.01.14371

<https://www.schmalz.com/10.01.01.14371>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 30 NBR-ESD-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 30


Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2.40 mm
Dmax(S)	31.50 mm
Ds	28.80 mm
G1	G1/8"-M
H	17 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	34 N
Volume	1.30 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	30
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Flat suction cup (round)

PFYN 30 NBR-ESD-55 G1/8-AG

Part no.:10.01.01.14371

<https://www.schmalz.com/10.01.01.14371>

Weight	7.90 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



PFY 30 NBR-ESD-55 N007

Part no.:10.01.01.14344

Size: 30

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A



SA-NIP N007 G1/8-AG DN240

Part no.:10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2.4 mm

Material: Aluminum

Spanner size SW2: 4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr