

Vacuum pump

EVE-TR 8 DC

Part no.:10.03.01.00288

<https://www.schmalz.com/10.03.01.00288>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 8 DC

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: Direct current
Sound level at 50 Hz: 60.5 dB(A)
Weight: 12 kg

Design Data



Attribute	Value
B	123 mm
B1	138 mm
B2	11.50 mm
d	8.40 mm
G3	G3/8"-F
H	196 mm
L	231 mm
L2	80 mm
X1	80 mm
Y1	100 mm

Technical Data

Attribute	Value
Suction rate at DC	9.70 m³/h
Voltage	24 – 48V DC
Rated power	500 W
Current type	DC
Current type	Direct current
Sound level at 50 Hz	60.50 dB(A)
Weight	12 kg
Product family	EVE-TR

Vacuum pump

EVE-TR 8 DC

Part no.:10.03.01.00288

<https://www.schmalz.com/10.03.01.00288>

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



VBV -850...0 G3/8-AG EVE 4-8

Part no.:10.03.01.00107

External diameter D: 23 mm

Max. vacuum: -850 mbar

Thread G1: G3/8"-M

Length L: 45 mm

Construction use: Pump EVE

Size: 4-8

Spare parts



FILT-EINS 50 28x51 PAP VF-3/8

Part no.:10.07.01.00014

Filter pore size: 50 µm

External diameter D: 27.5 mm

Length L: 50.5 mm

Filter material: Paper

Construction use: Filter VF

Size: 3/8

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr