

Vacuum pump

EVE-OG 40 AC3

Part no.:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 40 AC3

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Current type: three-phase current

Sound level at 50 Hz: 64 dB(A)


Suction rate (50 Hz): 40 m³/h

Rated power 50 Hz: 1.1 kW

Voltage at 50Hz: 230/400±10%

Weight: 38 kg

Design Data



Attribute	Value
B	284 mm
B2	15 mm
G3	G1-1/4"-F
G5	M8-F
H	260 mm
L	625 mm
L2	130 mm
X1	179 mm
X2	123 mm
Y1	238 mm
Y2	171 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	40 m ³ /h
Voltage at 50Hz	230/400±10%
Rated power 50 Hz	1.10 kW
Sound level at 50 Hz	64 dB(A)

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Vacuum pump

EVE-OG 40 AC3

Part no.:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>

Weight	38 kg
Protection type IP	IP 54
Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no.:10.07.02.00050

External diameter D: 40 mm

Measuring range: 0,0 ... 1,0 bar

Construction shape manometers: Connection at rear

Thread G1: G3/4"-M



MSS-K 2.5-4A

Part no.:10.04.04.00120

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Vacuum pump

EVE-OG 40 AC3

Part no.:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>



VOL 50

Part no.:10.03.03.00118

Reservoirs volume: 50 l

Height H: 235 mm

Add. function: Manometer, valve, filter



ZUB EVE-OG Ölablass-Kit

Part no.:22.09.03.00038

Construction use: Pump EVE-OG

Spare parts



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no.:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8162431
schmalz@schmalz.co.kr

Vacuum pump

EVE-OG 40 AC3

Part no.:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>



OEL EVE-OG 1L ANDEROL 555

Part no.:27.02.01.00055

Construction use: Pump EVE-OG



VST EVE-OG-25-40

Part no.:10.03.02.00060

Construction use: Pump EVE-OG

Size: 25-40

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8562403
schmalz@schmalz.co.kr