


Flexible suction cup mounting for adaptation to sloping surfaces



Thread G1: G1/4"-F
Thread G2: M10x1.25-M
Operating temperature: 0 ... 70 °C

Design Data



Attribute	Value
dn	2.80 mm
G1	G1/4"-F
G2	M10x1.25-M
L	32 mm
LG1	10.50 mm
LG2	8 mm
SW1	17 mm
W	12 °

Technical Data

Attribute	Value
Bending moment	8 Nm
Vertical load	500 N
Weight	26 g
Product family	FLK